


Parts Required:

- Bogen UTI 313 Controller
- Bogen VAR-1 Interface
- Power Supply for Var-1
- 600/600 ohm Transformer
- Spare Trunk & Analog Ports

The VAR-1 is used to give Contact Closure to the UTI 312 on it's Override Interface to allow for an External All Page at the same time All the Phone Sets are receiving a Page

The Trunk Port is used for Zone Paging
The Analog Port is used for All Call over Phones & Paging system

Normal Zone Paging





600/600
Xformer

Operation:

- o Zone Paging-User hits a button or dials an Access Code and then enters a zone
Page comes out Speaker Zones Only.
- o All Page- User hits a button or dials an Access Code
Page comes out Speakers and Phone Sets

Page Speakers & Sets All Zone

UTI 312



CONTACT CLOSURE (GND) CONTACT CLOSURE SOURCE (+5V)
DRY AUDIO INPUT DRY AUDIO INPUT
TIP (POSITIVE) RING (NEGATIVE)